

LAF KOMORA (komora z laminarnim pretokom zraka)

Waldner electronics, Nemčija

Komora z laminarnim pretokom zraka se uporablja, kadar potrebujemo aseptične pogoje dela.

Značilnosti:

- Komora z laminarnim pretokom ustvarja okolje prosto delcev s tem, da se zrak filtrira skozi visoko učinkovite HEPA filtre. Laminarne tokovnice zraka potekajo v horizontalni smeri proti nam.
- Komora je dodatno opremljena z UV lučko, ki omogoča sterilizacijo površine komore.

Lokacija: Katedra za farmacevtsko tehnologijo

LAF CABINET (laminar air flow)

Waldner electronics, Germany

The cabinet with laminar air flow is used when aseptic conditions are required during our work.

Properties:

- Laminar air flow cabinets create particle-free environments by projecting air through HEPA filter (high efficiency particulate air) and exhausting air in laminar flow across a work area in a horizontal direction.
- It is additionally equipped with UV lamp to sterilize the interior of the cabinet.

Location: Department of Pharmaceutical Technology